



12T C-Head Crimper, U Dies, CU/AL/ACSR Conn

By Burndy
Catalog # [Y750HSXT](#)

12-Ton C-Head Crimper, Self Cont Hyd, Uses U Dies, Copper, Aluminum, ACSR

Features

- Easy tool positioning with its 355 head rotation
- Patented rapid advance pump for faster crimps
- Comfort grip handles
- Audible "pop-off" pressure relief valve
- Handle drain trigger

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	
Buy American Compliant	Contact Manufacturer

Conductor

Crimping Ranges	• Copper: #14 sol. - 750 kcmil • Aluminum: #8 sol. - 750 kcmil • ACSR: #4 AWG - 556.5 kcmil
-----------------	---

Dimensions

Length	23.96 in
Weight	17.2 lb.
Height	2.86 in
Width	8.71 in
Jaw Width	1.65 in

Dimensions	23.96 in x 8.71 in x 2.86 in
------------	------------------------------

Force Related

Crimp Force Capacity	12 ton
----------------------	--------

General

Application - For Use On	Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding
Trade Name	HYPRESS™
Sub Brand	HYPRESS
Tool Type	Self-Contained Hydraulic Crimper
Product Type	12-Ton
Die Type	U Die
UPC	781810458600
Type	Crimper
UPC 12 Digit	781810458600
UPC 14 Digit GTIN	00781810458600

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Plastic Case

Product Assets

[Catalog \[English\]](#)