



6T 4-POINT® Dieless Latch Head Crimper, Guides

By Burndy
Catalog # [Y81K2](#)

6-Ton 4-POINT® Dieless Latch Head Crimper, Hyd Self-Contained, Guides, CU/AL

Features

- Dieless System with range taking capabilities
- 360° head rotation
- Flip top design
- Unique crimping guides for improved reliability and ease of use

Application

Crimping

Specifications

Buy American Compliant No

Conductor

- Crimping Ranges
- Copper: #8 AWG -1000 kcmil
 - Copper Flex: #8 AWG - 777.7 kcmil
 - Aluminum: #8 AWG - 750 kcmil

Dimensions

Weight 13.6 lb.
Height 7.7 in



Width 2.5 in
Length 23.9 in
Dimensions 23.9 in x 2.5 in x 7.7 in

Force Related

Crimp Force Capacity 6 ton

General

Tool Type Self-Contained Hydraulic Crimper
Product Type Tooling
Container Type Hard Case
Application - For Use On Copper, Aluminum Terminals and Splices, HYPLUG™

Die Type Dieless
UPC 621945660342
Trade Name 4-POINT®
Type Crimper
UPC 12 Digit 621945660342
Series 4-POINT® Series

Product Assets

[Catalog \[English\]](#)