




YA25L2NT14, Comp. Term., Cu, Standard, Narrow, 2-Hole

By Burndy

Catalog # [YA25L2NT14](#)

Copper Compression Terminal, 1/0 AWG Cu, 2-Hole, 1/2" Stud, .625" Spacing, Standard Barrel, Narrow Tongue, Tin Plated, UL/CSA



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	1/0 AWG
Conductor - Copper DLO Size Range	N/A
Conductor Size	1/0 AWG
Conductor - Copper Str Navy Size Range	100 (61) Navy
Conductor - Copper Str Navy Size	100 (61) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	1/0 AWG

Configuration

Physical Attribute - Number of Holes	2
--------------------------------------	---

Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.48 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	65 mm
Dimension - Outside Diameter inch	0.51 in
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	15/16
Dimension - Stud Size inch	1/4
Dimension - Stud Size fraction	1/4
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	7/8 in
Dimension - Z inch	0.36 in
Dimension - B Length inch	0.88 in
Dimension - D inch	1.30 in
Dimension - N inch	0.31 in
Dimension - Bolt Size inch	0.25
Dimension - Length Overall inch	2.56 in

General

Trade Name	HYLUG™
Die Index	12
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Pink
Sub Brand	TERMINALS, HYLUG
UPC	781810279977

Type	YA-L-2NT
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 14 Digit GTIN	00781810279977

Minimum Pack Quantity	1
Carton Quantity	25

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[French, English\]](#)

Logistics



A Hubbell brand