



YA26L3BRBOX500, Compression Terminal

By Burndy
Catalog # [YA26L3BRBOX500](#)

Copper Compression Terminal



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	2/O AWG
Conductor - Copper Str Navy Size Range	125 (61) Navy
Conductor - Copper Str Navy Size	125 (61) Navy
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size Range	2/O AWG
Conductor - Copper Str Size	2/O AWG

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
----------------	-------

Voltage - Maximum	35000
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.83 in
Dimension - Bolt Hole Size inch	0.33 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/16
Dimension - Bolt Size fraction	5/16
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	15/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.36 in
Dimension - L Length Overall mm	52 mm
Dimension - B Length inch	0.94 in
Dimension - Outside Diameter inch	0.56 in
Dimension - D inch	0.70 in
Dimension - N inch	0.34 in
Dimension - Hole Size mm	10 mm
Dimension - Bolt Size inch	0.3125
Dimension - Hole Size inch	0.38
Dimension - Length Overall inch	2.06 in
Dimension - Strip Length inch	1 in
Dimension - Stud Size inch	5/16
Dimension - Stud Size fraction	5/16

General

Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived
Color Code	Black
Trade Name	HYLUG™
Die Index	13
UPC	781810179642
Type	Standard Barrel, Tin Plated
Material	Copper
Finish Type	Bare
UPC 12 Digit	781810179642
UPC 14 Digit GTIN	00781810179642

Logistics

Minimum Pack Quantity	6
Pallet Quantity	72000
Carton Quantity	500

Product Assets

[Catalog \[English\]](#)



A Hubbell brand