



YA26LB, Comp. Term., Cu, 1-Hole, Standard, Bell End

By Burndy

Catalog # [YA26LB](#)

Copper Compression Terminal, 2/0 AWG, 1/0 Flex G,H,I,K,M, DLO
Cu, 1-Hole, 3/8" Stud, Standard Barrel, Belled End, Tin Plated,
UL/CSA

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Flex K Size Range	1/0 AWG
Conductor - Copper Flex K Size	1/0 AWG
Conductor - Copper Flex M Size Range	1/0 AWG
Conductor - Copper Flex M Size	1/0 AWG
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Flex I Size Range	1/0 AWG
Conductor - Copper Flex G Size	1/0 AWG
Conductor - Copper DLO Size Range	1/0 AWG
Conductor - Copper DLO Size	1/0 (275/#24) DLO
Conductor Size	2/0 AWG
Conductor - Copper Flex H Size	1/0 AWG



Conductor - Copper Flex G Size Range	1/0 AWG
Conductor - Copper Str Navy Size	125 (61) Navy
Conductor - Copper Solid Size Range	2/0 AWG
Conductor - Copper Solid Size	2/0 AWG
Conductor Type	CODE
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Copper Flex H Size Range	1/0 AWG
Conductor - Copper Flex I Size	1/0 AWG

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.83 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	57 mm
Dimension - Outside Diameter inch	0.56 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1 in
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	15/16 in
Dimension - Z inch	0.42 in

Dimension - B Length inch	0.93 in	UPC	781810502976
Dimension - D inch	0.83 in	Type	Standard Belled Barrel, Tin Plated
Dimension - N inch	0.41 in		
Dimension - Bolt Size inch	0.38	Material	Copper
Dimension - Length Overall inch	2.26 in	Plating Type	Tin - Electro Plated
		Finish Type	Tin-Plated
		UPC 12 Digit	781810502976
		UPC 14 Digit GTIN	00781810502976
General		Logistics	
Trade Name	HYLUG™	Carton Quantity	10
Die Index	13		
Feature - Barrel Type	Standard		
Feature - Barrel Style	Belled		
Plated	Y		
Color Code	Black		
Physical Attribute - Tongue Type	Standard		
Sub Brand	HYLUG		
		Product Assets	
		Catalog [English]	
		Installation Manual [English]	
		Installation Manual [English]	



A Hubbell brand