



## YA26LBR, Comp. Term., Cu, 1-Hole, Standard, Unplated

By Burndy  
Catalog # [YA26LBR](#)

Copper Compression Terminal, 2/0 AWG, 125 Navy Stranded Cu, 1-Hole, 3/8" Stud, Standard Barrel, Unplated



### Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

### Application

Wire Termination

### Specifications

|                                    |              |
|------------------------------------|--------------|
| Certification - ETL                | No           |
| Certification - UL Recognized      | No           |
| Standards - RoHS Compliance Status | CM           |
| Certification - cULus              | No           |
| Industry Standard(s)               | UL 486A-486B |
| UL Listed                          | Yes          |
| Certification - CSA Approved       | Yes          |

### Conductor

|                                   |               |
|-----------------------------------|---------------|
| Conductor Size                    | 2/0 AWG       |
| Conductor - Copper Str Navy Size  | 125 (61) Navy |
| Conductor - Material              | COPPER        |
| Conductor Type                    | CODE          |
| Conductor - Copper Str Size Range | 2/0 AWG       |
| Conductor - Copper Str Size       | 2/0 AWG       |

### Configuration

|                                      |                 |
|--------------------------------------|-----------------|
| Physical Attribute - Number of Holes | 1               |
| Number of Pad Holes                  | 1               |
| Connector Type                       | STANDARD BARREL |

### Current

|                   |       |
|-------------------|-------|
| Voltage Rating    | 35 kV |
| Voltage - Maximum | 35000 |

### Dimensions

|                                   |          |
|-----------------------------------|----------|
| Dimension - Pad Width inch        | 0.83 in  |
| Dimension - Bolt Hole Size inch   | 0.39 in  |
| Dimension - Hole Size fraction    | 3/8      |
| Dimension - Bolt Size fraction    | 3/8      |
| Physical Attribute - Tongue Angle | Straight |
| Dimension - B Length fraction     | 15/16 in |
| Dimension - Z inch                | 0.42 in  |
| Dimension - L Length Overall mm   | 56 mm    |
| Dimension - B Length inch         | 0.94 in  |
| Dimension - Outside Diameter inch | 0.56 in  |
| Dimension - D inch                | 0.83 in  |
| Dimension - N inch                | 0.41 in  |
| Dimension - Hole Size mm          | 10.4 mm  |
| Dimension - Bolt Size inch        | 0.38     |
| Dimension - Hole Size inch        | 0.41     |
| Dimension - Length Overall inch   | 2.19 in  |
| Dimension - Strip Length inch     | 1 in     |
| Dimension - Stud Size fraction    | 3/8      |

### General

|                        |                                                                              |
|------------------------|------------------------------------------------------------------------------|
| Feature - Barrel Type  | Standard                                                                     |
| Feature - Barrel Style | <ul style="list-style-type: none"><li>• Chamfered</li><li>• Skived</li></ul> |
| Plated                 | Y                                                                            |
| Color Code             | Black                                                                        |
| Trade Name             | HYLUG™                                                                       |
| Die Index              | 13                                                                           |
| UPC                    | 781810136102                                                                 |
| Material               | Copper                                                                       |
| Plating Type           | Tin - Bright                                                                 |
| Finish Type            | Bare                                                                         |
| UPC 12 Digit           | 781810136102                                                                 |
| UPC 14 Digit GTIN      | 00781810136102                                                               |

### Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 50    |
| Pallet Quantity       | 38400 |
| Carton Quantity       | 50    |



A Hubbell brand