



YA26T6, Comp. Term., Cu, 1-Hole, Long Barrel, No Skive

By Burndy

Catalog # [YA26T6](#)

Copper Compression Terminal, 2/0 AWG Code, 70mm2 2 Str, 1-Hole, 1/2" Stud, Long Barrel, No Skive



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	2/0 AWG
Conductor - Copper Str Navy Size	125 (61) Navy
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Copper Str Size	2/0 AWG

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.81 in
Dimension - Bolt Hole Size inch	0.52 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-1/2 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.61 in
Dimension - L Length Overall mm	82 mm
Dimension - B Length inch	1.50 in
Dimension - Outside Diameter inch	0.58 in
Dimension - N inch	0.69 in
Dimension - Thread Size	1/2
Dimension - Inside Diameter inch	0.43 in
Dimension - Hole Size mm	13.5 mm
Dimension - Bolt Size inch	0.5
Dimension - Hole Size inch	0.53
Dimension - Length Overall inch	3.22 in
Thickness - Pad	0.13 in
Dimension - Strip Length inch	1-9/16 in
Dimension - Stud Size fraction	1/2

General

Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Black
Trade Name	HYLUG™
Die Index	13
UPC	781810080313
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810080313
UPC 14 Digit GTIN	00781810080313

Logistics

Minimum Pack Quantity	20
-----------------------	----



A Hubbell brand