



YA272N, Comp. Term., Cu, 2-Hole, Long Barrel

By Burndy

Catalog # [YA272N](#)

Copper Compression Terminal, 3/0 AWG Cu, 2-Hole, 1/2" Stud, 1.75" Spacing, Long Barrel, Tin Plated



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	3/0 AWG
Conductor Size	3/0 AWG
Conductor - Copper Str Navy Size	150 (61) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	3/0 AWG

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2

Connector Type	LONG BARREL
----------------	-------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.91 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	127 mm
Dimension - Outside Diameter inch	0.62 in
Dimension - Thread Size	1/2
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56
Thickness - Pad	0.13 in
Dimension - Strip Length inch	1-9/16
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-1/2 in
Dimension - Z inch	0.64 in
Dimension - B Length inch	1.50 in
Dimension - N inch	0.63 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall inch	5.01 in

General

Trade Name	HYLUG™
Die Index	14
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Orange
Physical Attribute - Tongue Type	Standard
Sub Brand	HYLUG

UPC	781810503249
Type	Long Barrel, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810503249
UPC 14 Digit GTIN	00781810503249

Logistics

Minimum Pack Quantity	1
Carton Quantity	10

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[French, English\]](#)



A Hubbell brand