



YA27LNT38, Comp. Term., Cu, 1-Hole, Standard, Narrow

By Burndy

Catalog # [YA27LNT38](#)

Copper Compression Terminal, 3/0 AWG Cu, 1-Hole, 3/8" Stud, Standard Barrel, Narrow Tongue, Tin Plated



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	3/0 AWG
Conductor - Copper DLO Size Range	N/A
Conductor Size	3/0 AWG
Conductor - Copper Str Navy Size Range	150 (61) Navy
Conductor - Copper Str Navy Size	150 (61) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	3/0 AWG

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.73 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	67 mm
Dimension - Outside Diameter inch	0.62 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1-1/16
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1 in
Dimension - Z inch	0.73 in
Dimension - B Length inch	1.00 in
Dimension - D inch	1.14 in
Dimension - N inch	0.38 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	2.64 in

General

Trade Name	HYLUG™
Die Index	14
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Orange
Physical Attribute - Tongue Type	Standard
Sub Brand	HYLUG
UPC	781810018538

Type	YA-L-NT, Code Conductor	Pallet Quantity	23200
	Standard Barrel Narrow Tongue	Carton Quantity	100
Material	Copper	Product Assets Catalog [English] Installation Manual [English] Installation Manual [French, English]	
Plating Type	Tin - Electro Plated		
Finish Type	Tin-Plated		
UPC 14 Digit GTIN	00781810018538		
Logistics			

