



YA282LN, Comp. Term., Cu, 2-Hole, Standard Barrel

By Burndy
Catalog # [YA282LN](#)

Copper Compression Terminal, 4/0 AWG Cu, 2-Hole, 1/2" Stud, 1.75" Spacing, Standard Barrel, Tin Plated



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper DLO Size Range	N/A
Conductor Size	4/0 AWG
Conductor - Copper Str Navy Size Range	200 (61) Navy
Conductor - Copper Str Navy Size	200 (61) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	4/0 AWG

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.02 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Outside Diameter	0.69 in
Package Width	0.000 in
Dimension - L Length Overall mm	112 mm
Dimension - Outside Diameter inch	0.69 in
Bolt Size	1/2 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Length	4.41 in
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	7/8 in
Dimension - Z inch	0.65 in
Dimension - B Length inch	0.88 in
Dimension - D inch	3.03 in
Dimension - N inch	0.63 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall inch	4.41 in

General

Trade Name	HYLUG™
Die Index	15
Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived
Plated	Y
Color Code	Purple

Physical Attribute - Tongue	Standard
Type	
Sub Brand	HYLUG
UPC	781810503522
Type	Standard Barrel, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 14 Digit GTIN	00781810503522

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[French, English\]](#)



A Hubbell brand