



YA28L2TC14E245, Comp. Term, Cu, 2-Hole, Standard, 45 Deg Pad

By Burndy

Catalog # [YA28L2TC14E245](#)

Copper Compression Terminal, 4/0 AWG Cu, 2-Hole, 1/4" Stud, .75" Spacing, Standard Barrel, 45 Degree Pad Angle, Tin Plated



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper DLO Size Range	N/A
Conductor Size	4/0 AWG
Conductor - Copper Str Navy Size	200 (61) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	4/0 AWG

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.02 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	69 mm
Dimension - Outside Diameter inch	0.69 in
Dimension - Thread Size	1/4 in
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size inch	1/4
Dimension - Stud Size fraction	1/4
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue Angle	45 Degree
Angle - Pad	45 °
Dimension - B Length fraction	7/8 in
Dimension - Z inch	0.33 in
Dimension - B Length inch	0.88 in
Dimension - N inch	0.31 in
Dimension - Bolt Size inch	0.25
Dimension - Length Overall inch	2.71 in

General

Trade Name	HYLUG™
Die Index	15
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Purple
Physical Attribute - Tongue Type	Standard
UPC	781810019405
Type	Standard Barrel, Tin Plated

Material	Copper		
Plating Type	Tin plated		
Finish Type	Tin-Plated		
UPC 12 Digit	781810019405		
UPC 14 Digit GTIN	00781810019405		
		Logistics	
		Minimum Pack Quantity	10
		Carton Quantity	10
		Product Assets	



[Catalog \[English\]](#)