



YA2C2, Cu Compression, 2 AWG, 2-Hole, 5/16" Stud

By Burndy
Catalog # [YA2C2](#)

YA2C2, Cu Compression, 2 AWG, 2-Hole, 5/16" Stud, 3/4" Spacing, Long Barrel



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	2 AWG
Conductor Size	2 AWG
Conductor - Copper Str Navy Size Range	60 (37) Navy
Conductor - Copper Str Navy Size	60 (37) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	2 AWG

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.59 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/16
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	75 mm
Dimension - Outside Diameter inch	0.42 in
Dimension - Hole Size mm	10 mm
Dimension - Hole Size inch	0.38
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size fraction	5/16
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.50 in
Dimension - B Length inch	1.25 in
Dimension - D inch	1.59 in
Dimension - N inch	0.34 in
Dimension - Bolt Size inch	0.3125
Dimension - Length Overall inch	2.97 in

General

Trade Name	HYLUG™
Die Index	10
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Brown
UPC	781810500705
Type	Long Barrel, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810500705
UPC 14 Digit GTIN	00781810500705

Logistics

Minimum Pack Quantity 1
Carton Quantity 25

Temperature Rating 194

Product Assets

Operational

[Catalog \[English\]](#)



A Hubbell brand