



YA2C2NT14, Cu Comp, 2 AWG, 2-Hole, Narrow, Long

By Burndy

Catalog # [YA2C2NT14](#)

2 AWG Cu, 2-Hole, 1/4" Stud, 5/8" Spacing, Long Barrel, Narrow Tongue, Brown / 10 Index



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper DLO Size Range	N/A
Conductor Size	2 AWG
Conductor - Copper Str Navy Size Range	60 (37) Navy
Conductor - Copper Str Navy Size	60 (37) Navy
Conductor - Copper Solid Size Range	2 AWG
Conductor - Copper Solid Size	2 AWG
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size Range	2 AWG
Conductor - Copper Str Size	2 AWG

Configuration

Physical Attribute - Number of Holes	2
--------------------------------------	---

Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.48 in
Dimension - Bolt Hole Size inch	0.27 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-1/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.34 in
Dimension - L Length Overall mm	73 mm
Dimension - B Length inch	1.25 in
Dimension - Outside Diameter inch	0.42 in
Dimension - D inch	1.27 in
Dimension - N inch	0.31 in
Dimension - Hole Size mm	6.9 mm
Dimension - Bolt Size inch	0.25
Dimension - Hole Size inch	0.27
Dimension - Length Overall inch	2.86 in
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size fraction	1/4

General

Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Brown
Trade Name	HYLUG™
Die Index	10
UPC	781810439807
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated

UPC 14 Digit GTIN		00781810439807	Product Assets Catalog [English] Installation Manual [English] Installation Manual [French, English]
Logistics			
Minimum Pack Quantity		50	
Pallet Quantity		48000	
Carton Quantity		50	
 A Hubbell brand		© 2026 Hubbell Incorporated. All rights reserved BRDY-YA2C2NT14-SPEC-EN REV 5/2026	