



YA2CA9DT, Comp Term, 2 AWG AL, 2-Hole, Soldered Seam

By Burndy

Catalog # [YA2CA9DT](#)

2 AWG, AL, 2 Hole, 1/2" Stud 1-3/4" Hole Spacing, AL9CU, Prefilled with Oxide Inhibitor, Solder Seam



Features

- UL486A-486B Listed and CSA Certified
- Aluminum terminals are dual rated to accommodate both copper and aluminum wire and are indicated with AL-CU on the connector - AL9CU is UL Listed 90°C, up to 35kV, AL7CU is UL Listed 75°C, up to 35kV
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damage of the wire strands during insertion
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with wire size, die index, color code, and crimp location bands
- Factory pre-filled with PENETROX Type A13 oxide inhibitor
- Color coded end caps are factory inserted in the barrels to match the die color code and prevent foreign materials from entering the barrel
- Aluminum oxidation is not easily detected but causes resistance in a connection, it is imperative the proper preparation takes place prior to making an aluminum-to-aluminum connection

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper DLO Size Range	N/A
Conductor Size	2 AWG
Conductor - Material	ALUMINUM / COPPER
Wire Size	2 AWG
Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG

Conductor Type	CODE
Conductor - Copper Str Size Range	2 AWG
Conductor - Copper Str Size	2 AWG

Configuration

Physical Attribute - Number of Holes	2
Connector Type	DUAL RATED

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.88 in
Dimension - Bolt Hole Size inch	0.52 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-1/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.73 in
Dimension - L Length Overall mm	120 mm
Dimension - B Length inch	1.12 in
Dimension - Outside Diameter inch	0.53 in
Dimension - D inch	3.11 in
Dimension - N inch	0.63 in
Dimension - Thread Size	1/2
Dimension - Hole Size mm	14 mm
Dimension - Bolt Size inch	0.5
Dimension - Hole Size inch	0.56
Dimension - Length Overall inch	4.73 in
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size fraction	1/2

General

Feature - Barrel Type	Standard
-----------------------	----------

Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Pink
Trade Name	HYLUG™
Physical Attribute - Tongue	Standard
Type	
Die Index	348
UPC	781810439579
Material	ALUMINUM
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810439579
UPC 14 Digit GTIN	00781810439579

Logistics	
Pallet Quantity	24300
Carton Quantity	50

Operational	
Temperature Rating	194

Product Assets	
Catalog [English]	
Installation Manual [English]	
Installation Manual [English]	



A Hubbell brand