



YA2CL2TC38, 2 AWG Cu, 2 Hole, 3/8 Stud, Standard Barrel

By Burndy
Catalog # [YA2CL2TC38](#)

2 AWG, CU, 2 Hole, 3/8 Stud, 1 IN Spacing, Standard Barrel, Inspection Window

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	2 AWG
Conductor Size	2 AWG
Conductor - Copper Str Navy Size Range	60 (37) Navy
Conductor - Copper Str Navy Size	60 (37) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	2 AWG

Configuration



Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.60 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Outside Diameter	0.42 in
Package Width	0.000 in
Dimension - L Length Overall mm	77 mm
Dimension - Outside Diameter inch	0.42 in
Bolt Size	3/8 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	15/16
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Length	3.03 in
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.42 in
Dimension - B Length inch	0.88 in
Dimension - D inch	1.83 in
Dimension - N inch	0.41 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	3.03 in

General

Trade Name	HYLUG™
Die Index	10
Feature - Barrel Type	Standard
Feature - Barrel Style Plated	Chamfered Y

Color Code	Brown
Physical Attribute - Tongue	Standard
Type	
Sub Brand	HYLUG
UPC	781810018170
Type	Standard Barrel, Tin Plated
Material	Copper
Plating Type	Electro Tin Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810018170
UPC 14 Digit GTIN	00781810018170

Logistics

Minimum Pack Quantity	1
Carton Quantity	25

Operational

Temperature Rating	194
--------------------	-----

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[French, English\]](#)



A Hubbell brand