



YA2CL50, 2 AWG, 60 Navy, 1-Hole, 7/8" Stud, Standard Barrel

By Burndy

Catalog # [YA2CL50](#)

Copper compression terminal, Single hole W/ insp window, #2 AWG, 60 Navy, 7/8" Stud, 10 index, Brown



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	2 AWG
Conductor - Copper DLO Size Range	N/A
Conductor Size	2 AWG
Conductor - Copper Str Navy Size Range	60 (37) Navy
Conductor - Copper Str Navy Size	60 (37) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	2 AWG

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.19 in
Package Height	0.000 in
Dimension - Hole Size fraction	7/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	87 mm
Dimension - Outside Diameter inch	0.42 in
Width	1.19 in
Dimension - Hole Size mm	23.8 mm
Dimension - Hole Size inch	0.94
Dimension - Strip Length inch	15/16
Dimension - Stud Size fraction	7/8
Dimension - Bolt Hole Size inch	0.91 in
Dimension - Bolt Size fraction Length	7/8 3.42 in
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	7/8 in
Dimension - Z inch	0.89 in
Dimension - B Length inch Height	0.88 in 0.13 in
Dimension - D inch	1.77 in
Dimension - N inch	0.88 in
Dimension - Bolt Size inch	0.88
Dimension - Length Overall inch	3.42 in
Dimensions	3.42 in x 1.19 in x 0.13 in

General

Trade Name	HYLUG™
Die Index	10
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Brown
UPC	781810050118
Type	Standard Barrel, Tin Plated

Material	Copper	Minimum Pack Quantity	50
Plating Type	Tin - Electro Plated	Pallet Quantity	17400
Finish Type	Tin-Plated	Carton Quantity	50
UPC 14 Digit GTIN	00781810050118		

Logistics

Product Assets

[Catalog \[English\]](#)



A Hubbell brand