



YA2CLB, 2 AWG, 3 Flex G,H,I,K,M,DLO, 1-Hole, 5/16" Stud, Std

By Burndy
Catalog # [YA2CLB](#)

2 AWG, #3 FLEX G,H,I,K,M DLO, CU, 1 Hole, 5/16 Stud, Standard Barrel, Bell End



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Flex K Size	3 AWG
Conductor - Copper Flex M Size Range	3 AWG
Conductor - Copper Flex M Size	3 AWG
Conductor - Copper Str Size	2 AWG
Conductor - Copper Flex G Size	3 AWG
Conductor - Copper DLO Size	3 (125/#24) DLO
Conductor Size	2 AWG
Conductor - Copper Flex H Size	3 AWG
Conductor - Copper Str Navy Size Range	60 (37) Navy
Conductor - Copper Str Navy Size	60 (37) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	2 AWG
Conductor - Copper Flex I Size	3 AWG

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.61 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/16
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	49 mm
Dimension - Outside Diameter inch	0.42 in
Dimension - Hole Size mm	10 mm
Dimension - Hole Size inch	0.38
Dimension - Strip Length inch	5/16
Dimension - Stud Size fraction	5/16
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.36 in
Dimension - B Length inch	0.87 in
Dimension - D inch	0.70 in
Dimension - N inch	0.34 in
Dimension - Bolt Size inch	0.3125
Dimension - Length Overall inch	1.94 in

General

Trade Name	HYLUG™
Die Index	10
Feature - Barrel Type	Standard
Feature - Barrel Style	Belled
Plated	Y
Color Code	Brown

Physical Attribute - Tongue Type	Standard
UPC	781810017944
Type	Standard Belled Barrel, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810017944
UPC 14 Digit GTIN	00781810017944

Minimum Pack Quantity	25
Carton Quantity	25

Operational

Temperature Rating	194
--------------------	-----

Product Assets

- Catalog [\[English\]](#)
- Installation Manual [\[English\]](#)
- Installation Manual [\[English\]](#)

Logistics



A Hubbell brand