



YA2CLNT14, 2 AWG Cu, 1-Hole, 1/4 Stud, Std, Narrow Tongue

By Burndy

Catalog # [YA2CLNT14](#)

2 AWG, CU, 1 Hole, 1/4 Stud, Standard Barrel, Inspection Window, Narrow Tongue



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG
Conductor - Copper Str Size	2 AWG
Conductor - Copper DLO Size Range	N/A
Conductor Size	2 AWG
Conductor - Copper Str Navy Size Range	60 (37) Navy
Conductor - Copper Str Navy Size	60 (37) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	2 AWG

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1

Connector Type

STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.50 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	46 mm
Dimension - Outside Diameter inch	0.42 in
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	15/16
Dimension - Stud Size inch	1/4
Dimension - Stud Size fraction	1/4
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	7/8 in
Dimension - Z inch	0.31 in
Dimension - B Length inch	0.88 in
Dimension - D inch	0.56 in
Dimension - N inch	0.25 in
Dimension - Bolt Size inch	0.25
Dimension - Length Overall inch	1.80 in

General

Trade Name	HYLUG™
Die Index	10
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Brown
Sub Brand	HYLUG
UPC	781810018491
Type	YA-L-NT, Code Conductor Standard Barrel Narrow Tongue

Material	Copper	Carton Quantity	100
Plating Type	Tin - Electro Plated	Product Assets Catalog [English] Installation Manual [English] Installation Manual [French, English]	
Finish Type	Tin-Plated		
UPC 14 Digit GTIN	00781810018491		
Logistics			
Pallet Quantity	76800		

