



YA302LN, 300 kcmil Cu, 2-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy

Catalog # [YA302LN](#)

300 kcmil Cu, 2-Hole, 1/2" Stud, 1.75" Spacing, Standard Barrel, Tin Plated, White / 17 or 298 Index



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	300 KCMIL
Conductor - Copper DLO Size Range	N/A
Conductor Size	300 KCMIL
Conductor - Copper Str Navy Size Range	300 (91) Navy
Conductor - Copper Str Navy Size	300 (91) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	300 kcmil

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.20 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	118 mm
Dimension - Outside Diameter inch	0.81 in
Dimension - Thread Size	1/2
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56
Dimension - Strip Length inch	1 in
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1 in
Dimension - Z inch	0.64 in
Dimension - B Length inch	1.03 in
Dimension - D inch	3.02 in
Dimension - N inch	0.63 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall inch	4.63 in

General

Trade Name	HYLUG™
Die Index	19
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	White
Physical Attribute - Tongue Type	Standard
Sub Brand	HYLUG
UPC	781810504673

Type	Standard Barrel, Tin Plated	Carton Quantity	10
Material	Copper	Product Assets Catalog [English] Installation Manual [English] Installation Manual [French, English]	
Plating Type	Tin - Electro Plated		
Finish Type	Tin-Plated		
UPC 14 Digit GTIN	00781810504673		
Logistics			

