



YA30A7, 300 kcmil Al, 1-Hole, 1/4" Stud, Internal chamfer

By Burndy
Catalog # [YA30A7](#)

300 kcmil AL, 1-Hole Compression Lug, 1/4" Stud, AL9CU, Tin Plated, Prefilled with oxide inhibitor, end cap



Features

- UL486A-486B Listed and CSA Certified
- Aluminum terminals are dual rated to accommodate both copper and aluminum wire and are indicated with AL-CU on the connector - AL9CU is UL Listed 90°C, up to 35kV, AL7CU is UL Listed 75°C, up to 35kV
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damage of the wire strands during insertion
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with wire size, die index, color code, and crimp location bands
- Factory pre-filled with PENETROX Type A13 oxide inhibitor
- Color coded end caps are factory inserted in the barrels to match the die color code and prevent foreign materials from entering the barrel
- Aluminum oxidation is not easily detected but causes resistance in a connection, it is imperative the proper preparation takes place prior to making an aluminum-to-aluminum connection

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	ALUMINUM / COPPER
Wire Size	300 KCMIL
Conductor - AL Str Size	300 KCMIL
Conductor - AL Str Size Range	300 kcmil
Conductor - Copper Str Size	300 KCMIL
Conductor Size	300 KCMIL
Conductor Type	CODE

Conductor - Copper Str Size Range	300 kcmil
-----------------------------------	-----------

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	DUAL RATED

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.38 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	99 mm
Dimension - Outside Diameter inch	1.01 in
Dimension - Thread Size	1/4 in
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Stud Size fraction	1/4
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-7/16 in
Dimension - Z inch	0.74 in
Dimension - B Length inch	1.44 in
Dimension - D inch	1.37 in
Dimension - N inch	0.63 in
Dimension - Inside Diameter inch	0.65 in
Dimension - Bolt Size inch	0.25
Dimension - Length Overall inch	3.90 in

General

Trade Name	HYLUG™
------------	--------

Die Index	470
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Blue
Physical Attribute - Tongue Type	Standard
UPC	781810033579
Material	Aluminum
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810033579
UPC 14 Digit GTIN	00781810033579

Logistics

Minimum Pack Quantity	5
Carton Quantity	60

Operational

Temperature Rating	194
--------------------	-----

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[English\]](#)



A Hubbell brand