



YA30L, 300 kcmil, CU, 1 Hole, 1/2 Stud, Standard Barrel

By Burndy
Catalog # [YA30L](#)

300 kcmil, CU, 1 Hole, 1/2 Stud, Standard Barrel, Inspection Window, White / 17 or 298 Index



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	300 KCMIL
Conductor - Copper DLO Size Range	N/A
Conductor Size	300 KCMIL
Conductor - Copper Str Navy Size Range	300 (91) Navy
Conductor - Copper Str Navy Size	300 (91) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	300 kcmil

Configuration

Physical Attribute - Number of Holes 1

Number of Pad Holes 1
Connector Type STANDARD BARREL

Current

Voltage Rating 35 kV
Voltage - Maximum 35000

Dimensions

Dimension - Pad Width inch	1.20 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	68 mm
Dimension - Outside Diameter inch	0.81 in
Dimension - Hole Size mm	13 mm
Dimension - Strip Length inch	1-1/16
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1 in
Dimension - Z inch	0.55 in
Dimension - B Length inch	1.03 in
Dimension - D inch	1.08 in
Dimension - N inch	0.53 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall inch	2.69 in

General

Trade Name	HYLUG™
Die Index	17
Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived
Plated	Y
Color Code	White
Physical Attribute - Tongue Type	Standard
Sub Brand	HYLUG
UPC	781810504857

Type	Standard Barrel, Tin Plated	Minimum Pack Quantity	1
Material	Copper	Carton Quantity	10
Plating Type	Tin - Electro Plated	Product Assets Catalog [English] Installation Manual [English] Installation Manual [French, English]	
Finish Type	Tin-Plated		
UPC 14 Digit GTIN	00781810504857		
Logistics			



A Hubbell brand