



YA30LNT38G1, 300 kcmil Cu, 1-Hole, 3/8" Stud, Narrow Tongue

By Burndy

Catalog # [YA30LNT38G1](#)

HYLUG™ Copper Compression Terminal; Narrow Tongue;
Standard Barrel, 300 kcmil Cu, 1-Hole, 3/8" Stud



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	300 KCMIL
Conductor - Copper Str Navy Size Range	300 (91) Navy
Conductor - Copper Str Navy Size	300 (91) Navy
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size Range	300 kcmil
Conductor - Copper Str Size	300 KCMIL

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
----------------	-------

Voltage - Maximum	35000
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.82 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Hole Size fraction	3/8
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1 in
Dimension - Z inch	0.82 in
Dimension - L Length Overall mm	75 mm
Dimension - B Length inch	1.03 in
Dimension - Outside Diameter inch	0.81 in
Dimension - D inch	1.20 in
Dimension - N inch	0.38 in
Dimension - Thread Size	3/8
Dimension - Inside Diameter inch	0.65 in
Dimension - Hole Size mm	10.4 mm
Dimension - Bolt Size inch	0.38
Dimension - Hole Size inch	0.41
Dimension - Length Overall inch	2.97 in
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	White
Trade Name	HYLUG™
Die Index	17
UPC	781810163962
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810163962
UPC 14 Digit GTIN	00781810163962

Logistics

Minimum Pack Quantity	100
-----------------------	-----



A Hubbell brand