



YA30LTC38FX, 250 kcmil G,H, Cu, 1-Hole, 3/8" Stud, Standard

By Burndy

Catalog # [YA30LTC38FX](#)

250 kcmil, G,H, CU, 1 Hole, 3/8 Stud, Standard Barrel, Inspection Window



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	250 KCMIL
Conductor - Copper Str Size	250 KCMIL
Conductor - Copper Flex G Size	250 KCMIL
Conductor Size	250 KCMIL
Conductor - Copper Flex H Size	250 KCMIL
Conductor - Copper Flex G Size	250 kcmil
Range	
Conductor Type	FLEX
Conductor - Copper Str Size	300 kcmil
Range	
Conductor - Copper Flex H Size	250 kcmil
Range	

Configuration

Physical Attribute - Number of Holes	1
--------------------------------------	---

Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.20 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	62 mm
Dimension - Outside Diameter inch	0.81 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1-1/16 in
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.42 in
Dimension - B Length inch	1.03 in
Dimension - N inch	0.41 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	2.44 in


General

Trade Name	HYLUG™
Die Index	16
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Yellow
Sub Brand	HYLUG
UPC	781810020364
Type	YA-L-FX
Construction Material - Main	Copper tubing

Material	Copper	Pallet Quantity	14800
Plating Type	Tin	Carton Quantity	50
Finish Type	Tin-Plated		
UPC 12 Digit	781810020364		
UPC 14 Digit GTIN	00781810020364		

Logistics

Minimum Pack Quantity	1
-----------------------	---



Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[English\]](#)