



YA30LTC58FX, 250 kcmil G,H, Cu, 1-Hole, 5/8" Stud, Standard

By Burndy

Catalog # [YA30LTC58FX](#)

250 kcmil, G,H, CU, 1 Hole, 5/8 Stud, Standard Barrel, Inspection Window

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	250 KCMIL
Conductor - Copper Str Size	250 KCMIL
Conductor - Copper Flex G Size	250 KCMIL
Conductor Size	250 KCMIL
Conductor - Copper Flex H Size	250 KCMIL
Conductor - Copper Flex G Size	250 kcmil
Range	
Conductor Type	FLEX
Conductor - Copper Str Size	300 kcmil
Range	
Conductor - Copper Flex H Size	250 kcmil
Range	

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL



Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.20 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	5/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	75 mm
Dimension - Outside Diameter inch	0.81 in
Dimension - Hole Size mm	17.5 mm
Dimension - Hole Size inch	0.69
Dimension - Strip Length inch	1-1/16 in
Dimension - Stud Size inch	5/8
Dimension - Stud Size fraction	5/8
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.67 in
Dimension - B Length inch	1.03 in
Dimension - N inch	0.66 in
Dimension - Bolt Size inch	0.63
Dimension - Length Overall inch	2.94 in

General

Trade Name	HYLUG™
Die Index	16
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Yellow
UPC	781810034521
Type	Standard Barrel, Tin Plated
Material	Copper
Plating Type	Tin
Finish Type	Tin-Plated
UPC 12 Digit	781810034521

UPC 14 Digit GTIN		00781810034521	Product Assets Catalog [English] Installation Manual [English] Installation Manual [English]
Logistics			
Minimum Pack Quantity		1	
Pallet Quantity		14800	
Carton Quantity		50	
 A Hubbell brand		© 2026 Hubbell Incorporated. All rights reserved BRDY-YA30LTC58FX-SPEC-EN REV 5/2026	