



YA312LN, 350 kcmil Cu, 2-Hole, 1/2" Stud, 1.75" Spacing, Std

By Burndy
Catalog # [YA312LN](#)

350 kcmil, CU, 2 Hole, 1/2 Stud, 1-3/4 IN Spacing, Standard Barrel, Inspection Window



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	350 KCMIL
Conductor - Copper DLO Size Range	N/A
Conductor Size	350 KCMIL
Conductor - Copper Str Navy Size Range	350 (91) Navy
Conductor - Copper Str Navy Size	350 (91) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	350 kcmil

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2

Connector Type	STANDARD BARREL
----------------	-----------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.29 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	119 mm
Dimension - Outside Diameter inch	0.88 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-1/16 in
Dimension - Z inch	0.64 in
Dimension - B Length inch	1.06 in
Dimension - D inch	3.01 in
Dimension - N inch	0.62 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall inch	4.70 in

General

Trade Name	HYLUG™
Die Index	18
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Red
Physical Attribute - Tongue Type	Standard
Sub Brand	HYLUG
UPC	781810505076

Type	Standard Barrel, Tin Plated	Minimum Pack Quantity	1
Material	Copper	Carton Quantity	10
Plating Type	Tin - Electro Plated	Product Assets Catalog [English] Installation Manual [English] Installation Manual [French, English]	
Finish Type	Tin-Plated		
UPC 14 Digit GTIN	00781810505076		
Logistics			



A Hubbell brand