



YA322NNT, 400 kcmil CU, 2-Hole, NEMA Pad, Long, Narrow

By Burndy
Catalog # [YA322NNT](#)

400 kcmil, CU, 2 Hole, 1/2 Stud, 1-3/4 IN Spacing, Long Barrel, Narrow Tongue



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper DLO Size Range	N/A
Conductor Size	400 KCMIL
Conductor - Copper Str Navy Size	400 (127)
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size Range	400 kcmil
Conductor - Copper Str Size	400 KCMIL

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.96 in
Dimension - Bolt Hole Size inch	0.56 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	2-3/25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	148 mm
Dimension - B Length inch	2.12 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Hole Size mm	14 mm
Dimension - Bolt Size inch	0.5
Dimension - Hole Size inch	0.56
Dimension - Length Overall inch	5.85 in
Dimension - Strip Length inch	2-3/16 in
Dimension - Stud Size inch	1/2 in
Dimension - Stud Size fraction	1/2

General

Feature - Barrel Style Plated	Chamfered Y
Color Code	Blue
Trade Name	HYLUG™
Die Index	19
UPC	781810672792
Material	Copper
Plating Type	Tin
Finish Type	Tin-Plated
UPC 14 Digit GTIN	00781810672792

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5550
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[English\]](#)

[Installation Manual \[French, English\]](#)



A Hubbell brand