



YA32L2TC38, 400 kcmil Cu, 2-Hole, 3/8" on 1" Spacing, Std

By Burndy

Catalog # [YA32L2TC38](#)

400 kcmil, CU, 2 Hole, 3/8 Stud, 1 IN Spacing, Standard Barrel, Inspection Window



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	400 KCMIL
Conductor Size	400 KCMIL
Conductor - Copper Str Navy Size	400 (127) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	400 kcmil

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.40 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	94 mm
Dimension - Outside Diameter inch	0.95 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1-1/4
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-3/16 in
Dimension - Z inch	0.42 in
Dimension - B Length inch	1.19 in
Dimension - N inch	0.41 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	3.69 in

General

Trade Name	HYLUG™
Die Index	19
Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived
Plated	Y
Color Code	Blue
Physical Attribute - Tongue Type	Standard
UPC	781810018163
Type	Standard Barrel, Tin Plated
Material	Copper
Plating Type	Tin
Finish Type	Tin-Plated

UPC 12 Digit	781810018163	Carton Quantity	50
UPC 14 Digit GTIN	00781810018163		
Logistics		Product Assets	
Minimum Pack Quantity	1	Catalog [English]	
Pallet Quantity	7500	Installation Manual [English]	
		Installation Manual [French, English]	

