



YA32LTC7890, 400 kcmil, 1-Hole, 7/8", Standard, 90 Degree

By Burndy

Catalog # [YA32LTC7890](#)

400 kcmil Cu, 1-Hole, 7/8" Stud, Standard Barrel, Tin Plated, 90
Degree Pad Angle



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper DLO Size Range	N/A
Conductor Size	400 KCMIL
Conductor - Copper Str Navy Size	400 (127) Navy
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size Range	400 kcmil
Conductor - Copper Str Size	400 KCMIL

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.40 in
Dimension - Bolt Hole Size inch	0.91 in
Package Height	0.000 in
Dimension - Hole Size fraction	7/8
Dimension - Bolt Size fraction	7/8
Physical Attribute - Tongue Angle	90 Degree
Dimension - Height inch	2.19 in
Angle - Pad	90 °
Dimension - B Length fraction	1-3/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.89 in
Dimension - L Length Overall mm	60 mm
Dimension - B Length inch	1.19 in
Dimension - Outside Diameter inch	0.95 in
Dimension - N inch	0.88 in
Dimension - Hole Size mm	23.8 mm
Dimension - Bolt Size inch	0.88
Dimension - Hole Size inch	0.94
Dimension - Length Overall inch	2.38 in
Dimension - Strip Length inch	1-1/4
Dimension - Stud Size inch	7/8
Dimension - Stud Size fraction	7/8

General

Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived
Plated	Y
Color Code	Blue
Trade Name	HYLUG™
Die Index	19
UPC	781810314838
Type	Standard Barrel, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated

UPC 12 Digit	781810314838	Carton Quantity	10
UPC 14 Digit GTIN	00781810314838		
		Product Assets	
		Catalog [English]	

Logistics

Minimum Pack Quantity 10



A Hubbell brand