



YA34A12, Aluminum Stackable Terminal, Straight Lug

By Burndy
Catalog # [YA34A12](#)



Aluminum Stackable Terminal- Straight Lug, 500 Kcmil, Pink,1 hole,Tin - Electro Plated

Features

- Aluminum Stackable Terminal - Straight Lug
- 1-Hole, Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	500 kcmil
Conductor - AL Str Size Range	500 kcmil
Conductor - Copper Str Size	500 kcmil

Configuration

Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.62 in
Dimension - Hole Size fraction	5/9
Physical Attribute - Tongue Angle	Straight
Dimension - P inch	3.65 in

Dimension - L Length Overall mm	188 mm
Dimension - B Length inch	2.34 in
Dimension - Outside Diameter inch	1.32 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	7.42 in
Dimension - Strip Length inch	2-5/8

General

Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Pink
Trade Name	HYLUG™
Die Index	300
UPC	781810130711
Material	Aluminum
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810130711
UPC 14 Digit GTIN	00781810130711

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2880
Carton Quantity	12

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[English\]](#)
[Installation Manual \[English\]](#)



A Hubbell brand