



YA34L2TC38FX90, 350 kcmil Flex, 2-Hole, 3/8" on 1", 90 Deg

By Burndy

Catalog # [YA34L2TC38FX90](#)

350 kcmil Flex, G,H,I,K,M, 373 DLO, Cu, 2-Hole, 3/8" Stud, 1" Spacing, Standard Barrel, Inspection Window, 90 Degree Pad Angle, Blue / 19 Index

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	350 KCMIL
Conductor - Copper Flex K Size Range	350 kcmil
Conductor - Copper Flex K Size	350 KCMIL
Conductor - Copper Flex M Size Range	350 kcmil
Conductor - Copper Flex M Size	350 KCMIL
Conductor - Copper Str Size	350 KCMIL
Conductor - Copper Flex I Size Range	350 kcmil
Conductor - Copper Flex G Size	350 KCMIL
Conductor - Copper DLO Size Range	373 kcmil
Conductor - Copper DLO Size	373 KCMIL
Conductor Size	350 KCMIL
Conductor - Copper Flex H Size	350 KCMIL



Conductor - Copper Flex G Size Range	350 kcmil
Conductor Type	FLEX
Conductor - Copper Str Size Range	350 kcmil
Conductor - Copper Flex H Size Range	350 kcmil
Conductor - Copper Flex I Size	350 KCMIL

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.55 in
Package Height	0.000 in
Dimension - Height mm	61.7 mm
Dimension - Hole Size fraction	3/8
Dimension - Height inch	2.43 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	65 mm
Dimension - Outside Diameter inch	1.06 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	90 Degree
Angle - Pad	90 °
Dimension - B Length fraction	1-1/4 in
Dimension - Z inch	0.42 in
Dimension - B Length inch	1.27 in
Dimension - N inch	0.41 in

Dimension - Bolt Size inch	0.38	Type	Standard Barrel, Tin Plated
Dimension - Length Overall inch	2.54 in	Material	Copper
General		Plating Type	Tin
		Finish Type	Tin-Plated
		UPC 12 Digit	781810080412
		UPC 14 Digit GTIN	00781810080412
		Logistics	
		Minimum Pack Quantity	10
		Pallet Quantity	4640
Product Assets		Carton Quantity	10
		Product Assets	
		Catalog [English]	
Trade Name	HYLUG™		
Die Index	19		
Feature - Barrel Type	Standard		
Feature - Barrel Style	Chamfered		
Plated	Y		
Color Code	Blue		
Physical Attribute - Tongue	Standard		
Type			
UPC	781810080412		



A Hubbell brand