



YA34LTC58FX, 350 kcmil G,H,I,K,M, 373 DLO, Cu, 1-Hole, Std

By Burndy

Catalog # [YA34LTC58FX](#)

350 kcmil G,H,I,K,M,373 DLO, CU, 1 Hole, 5/8 Stud, Standard Barrel, Inspection Window

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	350 KCMIL
Conductor - Copper Flex K Size Range	350 kcmil
Conductor - Copper Flex K Size	350 KCMIL
Conductor - Copper Flex M Size Range	350 kcmil
Conductor - Copper Flex M Size	350 KCMIL
Conductor - Copper Str Size	350 KCMIL
Conductor - Copper Flex I Size Range	350 kcmil
Conductor - Copper Flex G Size	350 KCMIL
Conductor - Copper DLO Size Range	373 kcmil
Conductor - Copper DLO Size	373 KCMIL
Conductor Size	350 KCMIL
Conductor - Copper Flex H Size	350 KCMIL
Conductor - Copper Flex G Size Range	350 kcmil
Conductor Type	FLEX



Conductor - Copper Str Size Range	350 kcmil
Conductor - Copper Flex H Size Range	350 kcmil
Conductor - Copper Flex I Size	350 KCMIL

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.55 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	5/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	86 mm
Dimension - Outside Diameter inch	1.06 in
Dimension - Hole Size mm	17.5 mm
Dimension - Hole Size inch	0.69
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size inch	5/8
Dimension - Stud Size fraction	5/8
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-1/4 in
Dimension - Z inch	0.67 in
Dimension - B Length inch	1.27 in
Dimension - N inch	0.66 in
Dimension - Bolt Size inch	0.63
Dimension - Length Overall inch	3.37 in

General

Trade Name	HYLUG™	UPC 14 Digit GTIN	00781810018972
Die Index	19	Logistics	
Feature - Barrel Type	Standard		
Feature - Barrel Style	Chamfered		
Plated	Y		
Color Code	Blue	Minimum Pack Quantity	50
UPC	781810018972	Pallet Quantity	6000
Type	Standard Barrel, Tin Plated	Carton Quantity	50
Material	Copper	Product Assets	
Plating Type	Tin		
Finish Type	Tin-Plated		
UPC 12 Digit	781810018972		
		Catalog [English]	
		Installation Manual [English]	
		Installation Manual [English]	

