



YA36L2TC3845, 600 kcmil Cu, 2-Hole, 3/8" on 1", Std, 45 Deg

By Burndy

Catalog # [YA36L2TC3845](#)

600 kcmil, CU, 2 Hole, 3/8 Stud, 1 IN Spacing, Standard Barrel,
Inspection Window, 45 Degree



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	600 KCMIL
Conductor - Copper DLO Size Range	N/A
Conductor Size	600 KCMIL
Conductor Type	CODE
Conductor - Copper Str Size Range	600 kcmil

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.74 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Dimension - Height inch	2.48 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	107 mm
Dimension - Outside Diameter inch	1.19 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1-3/4
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	45 Degree
Angle - Pad	45 °
Dimension - B Length fraction	1-3/8 in
Dimension - Z inch	0.52 in
Dimension - B Length inch	1.38 in
Dimension - N inch	0.50 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	4.21 in

General

Trade Name	HYLUG™
Die Index	22
Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived
Plated	Y
Color Code	Green
Physical Attribute - Tongue Type	Standard
UPC	781810080078
Type	Standard Barrel, Tin Plated
Material	Copper

Plating Type	Tin - Electro Plated	Minimum Pack Quantity	20
Finish Type	Tin-Plated	Pallet Quantity	3000
UPC 12 Digit	781810080078	Carton Quantity	20
UPC 14 Digit GTIN	00781810080078		

Logistics

Product Assets

[Catalog \[English\]](#)



A Hubbell brand