



YA38L2NNTFX, 500 kcmil H,I,K, 550 kcmil G,H,I, 535 DLO Cu

By Burndy

Catalog # [YA38L2NNTFX](#)

500 kcmil H,I,K / 550 kcmil G,H,I,535 DLO, Cu, 2-Hole, 1/2" Stud, 1.75" Spacing, Standard Barrel, Inspection Window, Narrow Tongue, Tin Plated, Pink / L99 Index

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	500-550 KCMIL
Conductor - Copper Flex K Size Range	500 kcmil
Conductor - Copper Flex K Size	500 KCMIL
Conductor - Copper Flex M Size Range	500 kcmil
Conductor - Copper Flex M Size	500 KCMIL
Conductor - Copper Str Size	500-550 KCMIL
Conductor - Copper Flex I Size Range	500 / 550 kcmil
Conductor - Copper Flex G Size	550 KCMIL
Conductor - Copper DLO Size Range	535 kcmil
Conductor - Copper DLO Size	535 KCMIL
Conductor Size	500-550 KCMIL
Conductor - Copper Flex H Size	500-550 KCMIL



Conductor - Copper Flex G Size Range	550 kcmil
Conductor Type	FLEX
Conductor - Copper Str Size Range	500 / 550 kcmil
Conductor - Copper Flex H Size Range	500 / 550 kcmil
Conductor - Copper Flex I Size	500-550 KCMIL

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.63 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	136 mm
Dimension - Outside Diameter inch	1.25 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56
Dimension - Strip Length inch	1-7/16
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-7/16 in
Dimension - Z inch	0.65 in
Dimension - B Length inch	1.45 in
Dimension - D inch	3.03 in
Dimension - N inch	0.63 in
Dimension - Bolt Size inch	0.5

Dimension - Length Overall inch	5.35 in	Material	Copper
		Plating Type	Tin - Electro Plated
		Finish Type	Tin-Plated
		UPC 14 Digit GTIN	00781810034743
General		Logistics	
Trade Name	HYLUG™	Pallet Quantity	2160
Die Index	L99	Carton Quantity	30
Feature - Barrel Type	Standard		
Feature - Barrel Style	- Chamfered - Skived		
Plated	Y	Product Assets	
Color Code	Pink	Catalog [English]	
Sub Brand	TERMINALS, HYLUG	Installation Manual [English]	
UPC	781810034743	Installation Manual [English]	
Type	YAV-L-NTFX		



A Hubbell brand