



## YA392L, 750 kcmil Cu, 2-Hole, 3/8" Stud on 1-1/8", Std

By Burndy  
Catalog # [YA392L](#)

750 kcmil, Cu, 2-Hole, 3/8" Stud, 1.125" Spacing, Standard Barrel, Inspection Window, Tin Plated, Black / 24 Index



### Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

### Application

Wire Termination

### Specifications

|                               |              |
|-------------------------------|--------------|
| Certification - UL Recognized | No           |
| Certification - cULus         | No           |
| Industry Standard(s)          | UL 486A-486B |
| Certification - ETL           | No           |
| Standards - RoHS Compliance   | CM           |
| Status                        |              |
| UL Listed                     | Yes          |
| Certification - CSA Approved  | Yes          |

### Conductor

|                             |           |
|-----------------------------|-----------|
| Conductor - Material        | COPPER    |
| Conductor - Copper Str Size | 750 KCMIL |
| Conductor - Copper DLO Size | N/A       |
| Range                       |           |
| Conductor Size              | 750 KCMIL |
| Conductor Type              | CODE      |
| Conductor - Copper Str Size | 750 kcmil |
| Range                       |           |

### Configuration

|                                      |                 |
|--------------------------------------|-----------------|
| Physical Attribute - Number of Holes | 2               |
| Number of Pad Holes                  | 2               |
| Connector Type                       | STANDARD BARREL |

### Current

|                   |       |
|-------------------|-------|
| Voltage Rating    | 35 kV |
| Voltage - Maximum | 35000 |

### Dimensions

|                                   |           |
|-----------------------------------|-----------|
| Dimension - Pad Width inch        | 1.91 in   |
| Package Height                    | 0.000 in  |
| Dimension - Hole Size fraction    | 3/8       |
| Package Weight                    | 0.000 lb. |
| Package Length                    | 0.000 in  |
| Package Width                     | 0.000 in  |
| Dimension - L Length Overall mm   | 114 mm    |
| Dimension - Outside Diameter inch | 1.30 in   |
| Dimension - Hole Size mm          | 10.4 mm   |
| Dimension - Hole Size inch        | 0.41      |
| Dimension - Strip Length inch     | 1-15/16   |
| Dimension - Stud Size inch        | 3/8       |
| Dimension - Stud Size fraction    | 3/8       |
| Dimension - Bolt Hole Size inch   | 0.39 in   |
| Dimension - Bolt Size fraction    | 3/8       |
| Physical Attribute - Tongue Angle | Straight  |
| Dimension - B Length fraction     | 1-7/16 in |
| Dimension - Z inch                | 0.52 in   |
| Dimension - B Length inch         | 1.42 in   |
| Dimension - D inch                | 2.15 in   |
| Dimension - N inch                | 0.50 in   |
| Dimension - Bolt Size inch        | 0.38      |
| Dimension - Length Overall inch   | 4.48 in   |

### General

|                        |                                                                              |
|------------------------|------------------------------------------------------------------------------|
| Trade Name             | HYLUG™                                                                       |
| Die Index              | 24                                                                           |
| Feature - Barrel Type  | Standard                                                                     |
| Feature - Barrel Style | <ul style="list-style-type: none"><li>• Chamfered</li><li>• Skived</li></ul> |
| Plated                 | Y                                                                            |
| Color Code             | Black                                                                        |
| UPC                    | 781810522059                                                                 |
| Type                   | Standard Barrel, Tin Plated                                                  |
| Material               | Copper                                                                       |
| Plating Type           | Tin - Electro Plated                                                         |
| Finish Type            | Tin-Plated                                                                   |
| UPC 14 Digit GTIN      | 00781810522059                                                               |

### Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 10   |
| Pallet Quantity       | 2900 |
| Carton Quantity       | 10   |

Product Assets

- Catalog [English]
- Installation Manual [English]
- Installation Manual [French, English]



A Hubbell brand