



YA39L2TC38E10FX, 600 kcmil G,H,I,K, 1470 DLO, Cu, 2-Hole

By Burndy
Catalog # [YA39L2TC38E10FX](#)

600 kcmil G,H,I,K, 1470/24 DLO, CU, 2 Hole, 3/8 Stud, 1-3/4 IN Spacing, Standard Barrel, Inspection Window

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Flex G Size	600 KCMIL
Conductor - Copper DLO Size	1470/24
Range	
Conductor - Copper DLO Size	600 KCMIL
Conductor Size	600 KCMIL
Conductor - Copper Flex H Size	600 KCMIL
Conductor - Copper Flex G Size	600 kcmil
Range	
Conductor - Material	COPPER
Wire Size	600 KCMIL
Conductor - Copper Flex K Size	600 kcmil
Range	
Conductor - Copper Flex K Size	600 KCMIL
Conductor - Copper Flex M Size	600 kcmil
Conductor Type	FLEX
Conductor - Copper Flex I Run	600 KCMIL
Conductor - Copper Str Size	600 kcmil
Range	



Conductor - Copper Flex H Size	600 kcmil
Range	
Conductor - Copper Flex I Size	600 kcmil
Conductor - Copper Flex I Size	600 kcmil
Range	

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.91 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	3/8
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	117 mm
Dimension - B Length inch	1.42 in
Dimension - Hole Size mm	10.4 mm
Dimension - Bolt Size inch	0.38
Dimension - Hole Size inch	0.41
Dimension - Length Overall inch	4.61 in
Dimension - Strip Length inch	1-1/2
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Purple
Trade Name	HYLUG™

Die Index	23
UPC	781810539712
Type	Standard Barrel, Tin Plated
Material	Copper
Plating Type	Tin
Finish Type	Tin-Plated
UPC 14 Digit GTIN	00781810539712

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[English\]](#)



A Hubbell brand