



YA39LNT58, 750 kcmil Cu, 1-Hole, 5/8" Stud, Narrow Tongue

By Burndy

Catalog # [YA39LNT58](#)

750 kcmil, CU, 1 Hole, 5/8 Stud, Standard Barrel, Inspection Window, Narrow Tongue



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper DLO Size Range	N/A
Conductor Size	750 KCMIL
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size Range	750 kcmil
Conductor - Copper Str Size	750 KCMIL

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.30 in
Dimension - Bolt Hole Size inch	0.66 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/8
Dimension - Bolt Size fraction	5/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-7/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.77 in
Dimension - L Length Overall mm	93 mm
Dimension - B Length inch	1.42 in
Dimension - Outside Diameter inch	1.30 in
Dimension - D inch	1.43 in
Dimension - N inch	0.66 in
Dimension - Hole Size mm	17.5 mm
Dimension - Bolt Size inch	0.63
Dimension - Hole Size inch	0.69
Dimension - Length Overall inch	3.67 in
Dimension - Strip Length inch	1-15/16
Dimension - Stud Size inch	5/8
Dimension - Stud Size fraction	5/8

General

Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived
Plated	Y
Color Code	Black
Trade Name	HYLUG™
Die Index	24
UPC	781810498248
Material	Copper
Plating Type	Tin
Finish Type	Tin-Plated
UPC 14 Digit GTIN	00781810498248

Logistics

Minimum Pack Quantity	1
-----------------------	---

Pallet Quantity 4500
Carton Quantity 25

Product Assets

- Catalog [English]
- Installation Manual [English]
- Installation Manual [French, English]



A Hubbell brand