



YA3CLB, 3 AWG, 4 Flex G,H,I,K,M, DLO, Cu, 1-Hole, 5/16", Std

By Burndy
Catalog # [YA3CLB](#)

3 AWG, #4 FLEX G,H,I,K,M DLO, CU, 1 Hole, 5/16 Stud, Standard Barrel, Bell End

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Flex K Size	4 AWG
Conductor - Copper Flex M Size Range	4 AWG
Conductor - Copper Flex M Size	4 AWG
Conductor - Copper Str Size	3 AWG
Conductor - Copper Flex G Size	4 AWG
Conductor - Copper DLO Size	4 (105/#24) DLO
Conductor Size	3 AWG
Conductor - Copper Flex H Size	4 AWG
Conductor - Copper Str Navy Size Range	50 (19) Navy
Conductor - Copper Str Navy Size	50 (19) Navy
Conductor Type	CODE



Conductor - Copper Str Size Range 3 AWG

Conductor - Copper Flex I Size 4 AWG

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.55 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/16
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	49 mm
Dimension - Outside Diameter inch	0.38 in
Dimension - Hole Size mm	10 mm
Dimension - Hole Size inch	0.38
Dimension - Strip Length inch	15/16
Dimension - Stud Size fraction	5/16
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.36 in
Dimension - B Length inch	0.88 in
Dimension - D inch	0.70 in
Dimension - N inch	0.34 in
Dimension - Bolt Size inch	0.3125
Dimension - Length Overall inch	1.92 in

General

Trade Name	HYLUG™
Die Index	9
Feature - Barrel Type	Standard

Feature - Barrel Style	Belled	UPC 14 Digit GTIN	00781810501306
Plated	Y	Logistics	
Color Code	White	Minimum Pack Quantity	1
Physical Attribute - Tongue	Standard	Carton Quantity	25
Type		Operational	
Sub Brand	HYLUG	Temperature Rating	194
UPC	781810501306	Product Assets	
Type	Standard Belled Barrel, Tin Plated	Catalog [English]	
Material	Copper	Installation Manual [English]	
Plating Type	Tin Plated	Installation Manual [English]	
Finish Type	Tin-Plated		
UPC 12 Digit	781810501306		



A Hubbell brand