



YA42A3, 900 kcmil AL, 1-Hole, 5/8" Stud, AL9CU

By Burndy
Catalog # [YA42A3](#)

900 kcmil, AL, 1-Hole, 5/8" Stud, AL9CU, Prefilled with oxide inhibitor, End Cap, Tin Plated



Features

- UL486A-486B Listed and CSA Certified
- Aluminum terminals are dual rated to accommodate both copper and aluminum wire and are indicated with AL-CU on the connector - AL9CU is UL Listed 90°C, up to 35kV, AL7CU is UL Listed 75°C, up to 35kV
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damage of the wire strands during insertion
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with wire size, die index, color code, and crimp location bands
- Factory pre-filled with PENETROX Type A13 oxide inhibitor
- Color coded end caps are factory inserted in the barrels to match the die color code and prevent foreign materials from entering the barrel
- Aluminum oxidation is not easily detected but causes resistance in a connection, it is imperative the proper preparation takes place prior to making an aluminum-to-aluminum connection

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	900 KCMIL
Conductor - Material	ALUMINUM / COPPER
Wire Size	900 KCMIL
Conductor - AL Str Size	900 KCMIL
Conductor - AL Str Size Range	900 kcmil
Conductor Type	CODE

Conductor - Copper Str Size Range	600 kcmil
Conductor - Copper Str Size	900 KCMIL

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	DUAL RATED

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	2.14 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/8
Dimension - Bolt Size fraction	5/8
Physical Attribute - Tongue Angle	Straight
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	1.00 in
Dimension - L Length Overall mm	135 mm
Dimension - D inch	1.36 in
Dimension - N inch	0.63 in
Dimension - Hole Size mm	17.5 mm
Dimension - Bolt Size inch	0.63
Dimension - Hole Size inch	0.69
Dimension - Length Overall inch	5.32 in
Dimension - Strip Length inch	2 7/8
Dimension - Stud Size inch	5/8
Dimension - Stud Size fraction	5/8


General

Feature - Barrel Type Plated	Standard Y
Color Code	Gray
Trade Name	HYLUG™
Physical Attribute - Tongue Type	Standard

Die Index	303
UPC	781810637159
Material	Aluminum
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810637159
UPC 14 Digit GTIN	00781810637159

Logistics

Minimum Pack Quantity	3
-----------------------	---



Carton Quantity	3
-----------------	---

Operational

Temperature Rating	194
--------------------	-----

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[English\]](#)