



YA44L2NT38FX45, 750 kcmil G,H, 777 DLO Cu, 2-Hole, Std, Nrrw

By Burndy

Catalog # [YA44L2NT38FX45](#)

750 kcmil G,H,777 DLO, CU, 2 Hole, 3/8 Stud, 1 IN Spacing,
Standard Barrel, Inspection Window, Narrow Tongue, 45 Degree

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	750 KCMIL
Conductor - Copper Flex K Size	750
Conductor - Copper Flex M Size	750
Conductor - Copper Str Size	750 KCMIL
Conductor - Copper Flex I Size	750 kcmil
Range	
Conductor - Copper Flex G Size	750 KCMIL
Conductor - Copper DLO Size	777 kcmil
Range	
Conductor - Copper DLO Size	777 KCMIL
Conductor Size	750 KCMIL
Conductor - Copper Flex H Size	750 KCMIL
Conductor - Copper Flex G Size	750 kcmil
Range	
Conductor - Copper Solid Size	750 kcmil/FLEX
Conductor Type	FLEX



Conductor - Copper Str Size	750 kcmil
Range	
Conductor - Copper Flex H Size	750 kcmil
Range	
Conductor - Copper Flex I Size	750 KCMIL

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.63 in
Package Height	0.000 in
Dimension - Height mm	78 mm
Dimension - Hole Size fraction	3/8
Dimension - Height inch	3.07 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	120 mm
mm	
Dimension - Outside Diameter	1.5 in
inch	
Dimension - Thread Size	3/8
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1-5/8 in
Dimension - Stud Size inch	3/8 in
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	3/8 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue	45 Degree
Angle	
Angle - Pad	45 °
Dimension - Z inch	0.53 in
Dimension - B Length inch	1.65 in
Dimension - N inch	0.50 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall	4.71 in
inch	

General

Trade Name	HYLUG™
Die Index	L115
Feature - Barrel Type	Standard
Feature - Barrel Style	- Chamfered - Skived
Plated	Y
Color Code	Yellow
Physical Attribute - Tongue Type	Straight
Sub Brand	HYLUG
UPC	781810080429
Type	Standard Barrel, Tin Plated

Material	Copper
Plating Type	Tin -Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810080429
UPC 14 Digit GTIN	00781810080429

Logistics

Pallet Quantity	1480
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)



A Hubbell brand