



YA44L2NTC12E24, 1000 kcmil Cu, 2-Hole, Standard, Narrow

By Burndy
Catalog # [YA44L2NTC12E24](#)

1000 kcmil, CU, 2 Hole, 1/2 Stud, 1.85 IN Spacing, Standard Barrel, Inspection Window, Narrow Tongue



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper DLO Size Range	N/A
Conductor Size	1000 KCMIL
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size Range	1000 kcmil
Conductor - Copper Str Size	1000 KCMIL

Configuration

Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.63 in
Dimension - Hole Size fraction	1/2
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - L Length Overall mm	144 mm
Dimension - B Length inch	1.65 in
Dimension - Hole Size mm	13.5 mm
Dimension - Bolt Size inch	0.5
Dimension - Hole Size inch	0.53
Dimension - Length Overall inch	5.65 in
Dimension - Strip Length inch	1-15/16
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2

General

Plated	Y
Color Code	White
Trade Name	HYLUG™
Die Index	27
UPC	781810529249
Material	Copper
Plating Type	Tin
Finish Type	Tin-Plated
UPC 12 Digit	781810529249
UPC 14 Digit GTIN	00781810529249

Logistics

Minimum Pack Quantity	14
Pallet Quantity	1440
Carton Quantity	20

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)
[Installation Manual \[French, English\]](#)



A Hubbell brand