



YA44L2TC38, 1000 kcmil Cu, 2-Hole, Standard Barrel

By Burndy

Catalog # [YA44L2TC38](#)

1000 kcmil, Cu, 2-Hole, 3/8" Stud, 1" Spacing, Standard Barrel, Inspection Window, Tin Plated



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	1000 KCMIL
Conductor Size	1000 KCMIL
Conductor - Copper Solid Size	1000 kcmil
Conductor Type	CODE
Conductor - Copper Str Size Range	1000 kcmil

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
----------------	-------

Voltage - Maximum	35000
-------------------	-------

Dimensions


Dimension - Pad Width inch	2.19 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	120 mm
Dimension - Outside Diameter inch	1.5 in
Dimension - Thread Size	3/8
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1-15/16
Dimension - Stud Size inch	3/8 in
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	3/8 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.53 in
Dimension - B Length inch	1.65 in
Dimension - N inch	0.50 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	4.74 in

General

Trade Name	HYLUG™
Die Index	27
Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived
Plated	Y
Color Code	White
Physical Attribute - Tongue Type	Straight
UPC	781810020951
Type	Standard Barrel, Tin Plated
Material	Copper
Plating Type	Tin -Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810020951

Logistics

Minimum Pack Quantity3



Product Assets

[Catalog \[English\]](#)