



YA44L2TC38FX, 750 kcmil G, H, 777 DLO Cu, 2-Hole, Standard

By Burndy

Catalog # [YA44L2TC38FX](#)

750 kcmil G,H,777 DLO, CU, 2 Hole, 3/8 Stud, 1 IN Spacing,
Standard Barrel, Inspection Window

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	750 KCMIL
Conductor - Copper Flex K Size	750
Conductor - Copper Flex M Size	750
Conductor - Copper Str Size	750 KCMIL
Conductor - Copper Flex I Size	750 kcmil
Range	
Conductor - Copper Flex G Size	750 KCMIL
Conductor - Copper DLO Size	777 kcmil
Range	
Conductor - Copper DLO Size	777 KCMIL
Conductor Size	750 KCMIL
Conductor - Copper Flex H Size	750 KCMIL
Conductor - Copper Flex G Size	750 kcmil
Range	
Conductor - Copper Solid Size	750 kcmil/FLEX
Conductor Type	FLEX



Conductor - Copper Str Size	750 kcmil
Range	
Conductor - Copper Flex H Size	750 kcmil
Range	
Conductor - Copper Flex I Size	750 KCMIL

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	2.19 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	120 mm
mm	
Dimension - Outside Diameter	1.5 in
inch	
Dimension - Thread Size	3/8
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1-5/8 in
Dimension - Stud Size inch	3/8 in
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	3/8 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue	Straight
Angle	
Dimension - Z inch	0.53 in
Dimension - B Length inch	1.65 in
Dimension - N inch	0.50 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall	4.74 in
inch	

General

Trade Name	HYLUG™	Plating Type	Tin -Plated
Die Index	L115	Finish Type	Tin-Plated
Feature - Barrel Type	Standard	UPC 12 Digit	781810020999
Feature - Barrel Style	• Chamfered • Skived	UPC 14 Digit GTIN	00781810020999
Plated	Y	Logistics	
Color Code	Yellow	Pallet Quantity	1960
Physical Attribute - Tongue Type	Straight	Carton Quantity	10
Sub Brand	HYLUG	Product Assets	
UPC	781810020999	Catalog [English]	
Type	Standard Barrel, Tin Plated	Installation Manual [English]	
Material	Copper	Installation Manual [English]	



A Hubbell brand