



YA452N, 1250 kcmil Cu, 2-Hole NEMA, Long Barrel

By Burndy
Catalog # [YA452N](#)

1250 kcmil, CU, 2 Hole, 1/2 Stud, 1-3/4" Spacing, Long Barrel, Tin Plated, Yellow / 29 Index



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	1250 KCMIL
Conductor - Copper DLO Size Range	N/A
Conductor Size	1250 KCMIL
Conductor Type	CODE
Conductor - Copper Str Size Range	1250 kcmil

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	2.46 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	189 mm
Dimension - Outside Diameter inch	1.69 in
Dimension - Thread Size	1/2
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Strip Length inch	3-1/4
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	3-3/16 in
Dimension - Z inch	0.64 in
Dimension - B Length inch	3.19 in
Dimension - D inch	3.02 in
Dimension - N inch	0.63 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall inch	7.44 in

General

Trade Name	HYLUG™
Die Index	29
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Yellow
Sub Brand	HYLUG
UPC	781810524503
Type	Long Barrel, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated


UPC 12 Digit781810524503

UPC 14 Digit GTIN00781810524503

Logistics

Pallet Quantity882

Carton Quantity3



Product Assets

- Catalog [English]
- Installation Manual [English]
- Installation Manual [French, English]