



YA464N, 1500 kcmil Cu, 4-Hole NEMA, Long Barrel

By Burndy
Catalog # [YA464N](#)

1500 kcmil, Cu, 4-Hole, 1/2" Stud, 1-3/4" Spacing, Long Barrel, No Inspection Window, Green / 31 Index



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	1500 KCMIL
Conductor Size	1500 KCMIL
Conductor Type	CODE
Conductor - Copper Str Size Range	1500 kcmil

Configuration

Physical Attribute - Number of Holes	4
Number of Pad Holes	4
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
----------------	-------

Voltage - Maximum	35000
-------------------	-------

Dimensions

Dimension - Pad Width inch	3.00 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	192 mm
Dimension - Outside Diameter inch	1.84 in
Dimension - Thread Size	1/2
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Strip Length inch	3-1/4
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.64 in
Dimension - B Length inch	3.19 in
Dimension - N inch	0.63 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall inch	7.55 in

General

Trade Name	HYLUG™
Die Index	31
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Green
Sub Brand	HYLUG
UPC	781810086056
Type	Long Barrel, Tin Plated
Material	Copper
Plating Type	Tin plated
Finish Type	Tin-Plated
UPC 12 Digit	781810086056

UPC 14 Digit GTIN	00781810086056	Product Assets
Logistics		Catalog [English]
Pallet Quantity	720	Installation Manual [English]
Carton Quantity	6	Installation Manual [French, English]

