



YA48A3, 2000 kcmil AL, 2-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YA48A3](#)

2000 kcmil, AL, 2 Hole, 1/2" Stud 1-3/4" Hole Spacing, Prefilled with oxide inhibitor, End Cap, AL9CU

Features

- UL486A-486B Listed and CSA Certified
- Aluminum terminals are dual rated to accommodate both copper and aluminum wire and are indicated with AL-CU on the connector - AL9CU is UL Listed 90°C, up to 35kV, AL7CU is UL Listed 75°C, up to 35kV
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damage of the wire strands during insertion
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with wire size, die index, color code, and crimp location bands
- Factory pre-filled with PENETROX Type A13 oxide inhibitor
- Color coded end caps are factory inserted in the barrels to match the die color code and prevent foreign materials from entering the barrel
- Aluminum oxidation is not easily detected but causes resistance in a connection, it is imperative the proper preparation takes place prior to making an aluminum-to-aluminum connection

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Material	ALUMINUM / COPPER
Wire Size	2000 KCMIL
Conductor - AL Str Size	2000 KCMIL
Conductor - AL Str Size Range	2000 kcmil
Conductor - Copper Str Size	2000 KCMIL
Conductor Size	2000 KCMIL
Conductor Type	CODE



Conductor - Copper Str Size Range	2000 kcmil
-----------------------------------	------------

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	DUAL RATED

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	3.57 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	216 mm
Dimension - Outside Diameter inch	2.60 in
Dimension - Thread Size	1/2
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56
Dimension - Strip Length inch	4 1/8
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	3-11/16 in
Dimension - Z inch	0.73 in
Dimension - B Length inch	3.69 in
Dimension - D inch	3.11 in
Dimension - N inch	0.63 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall inch	8.49 in

General

Trade Name	HYLUG™
------------	--------

Die Index	479
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Red
Physical Attribute - Tongue Type	Standard
UPC	781810763100
Material	Aluminum
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810763100
UPC 14 Digit GTIN	00781810763100

Logistics	
Minimum Pack Quantity	4
Pallet Quantity	960
Carton Quantity	4

Operational	
Temperature Rating	194

Product Assets	
Catalog [English]	
Installation Manual [English]	
Installation Manual [English]	



A Hubbell brand