



YA48N, 2000 kcmilCu, 1-Hole, 1/2" Stud, Long Barrel

By Burndy
Catalog # [YA48N](#)



2000 kcmil, CU, 1 Hole, 1/2 Stud, Tin Plated, Long Barrel, Brown / 34 Index

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	2000 KCMIL
Conductor Size	2000 KCMIL
Conductor Type	CODE
Conductor - Copper Str Size Range	2000 kcmil

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	3.1 in
Package Height	0.000 in

Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	158 mm
Dimension - Outside Diameter inch	2.13 in
Dimension - Thread Size	1/2
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56
Dimension - Strip Length inch	3-1/2 in
Dimension - Stud Size inch	1/2 in
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.81 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	3-7/16 in
Dimension - Z inch	0.64 in
Dimension - B Length inch	3.44 in
Dimension - D inch	1.27 in
Dimension - N inch	0.63 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall inch	6.22 in

General

Trade Name	HYLUG™
Die Index	34
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Brown
Physical Attribute - Tongue Type	Straight
UPC	781810317112
Type	Long barrel, Tin-Plated
Material	Copper
Plating Type	Electro-Tin
Finish Type	Tin-Plated
UPC 12 Digit	781810317112
UPC 14 Digit GTIN	00781810317112

Logistics

Minimum Pack Quantity	3
-----------------------	---

Pallet Quantity 666
Carton Quantity 3

Product Assets

- Catalog [English]
- Installation Manual [English]
- Installation Manual [French, English]

Operational

Temperature Rating 194

