



YA48N90, 2000 kcmil Cu, 1/2" Stud, Long Barrel, 90 Degree

By Burndy

Catalog # [YA48N90](#)

2000 kcmil, CU, 1 Hole, 1/2 Stud, Long Barrel, Tin Plated, 90 Degree, Brown / 34 Index



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color

Application

Wire Termination

Specifications

Standards - RoHS Compliance	CM
Status	
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	2000 KCMIL
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size Range	2000 kcmil
Conductor - Copper Str Size	2000 KCMIL

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	3.10 in
Dimension - Bolt Hole Size inch	0.52 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Dimension - Bolt Size fraction	1/2

Physical Attribute - Tongue Angle	90 Degree
Dimension - Height inch	5.80 in
Angle - Pad	90 °
Dimension - B Length fraction	3-7/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.64 in
Dimension - L Length Overall mm	67 mm
Dimension - B Length inch	3.44 in
Dimension - Outside Diameter inch	0.34 in
Dimension - D inch	1.27 in
Dimension - N inch	0.63 in
Dimension - Thread Size	1/2
Dimension - Hole Size mm	14 mm
Dimension - Bolt Size inch	0.5
Dimension - Hole Size inch	0.56
Dimension - Length Overall inch	2.64 in
Dimension - Strip Length inch	3-1/2
Dimension - Stud Size fraction	1/2

General

Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Brown
Trade Name	HYLUG™
Die Index	34
UPC	781810317136
Type	Long Barrel, Tin Plated
Material	Copper
Plating Type	Tin
Finish Type	Tin-Plated
UPC 12 Digit	781810317136
UPC 14 Digit GTIN	00781810317136

Logistics

Minimum Pack Quantity	1
-----------------------	---

Operational

Temperature Rating	194
--------------------	-----



A Hubbell brand