



YA4C2L3, 4 AWG Cu, 2-Hole, 5/16" Stud, 7/8" Spacing, Std

By Burndy

Catalog # [YA4C2L3](#)

Copper Tubing Terminal, 2 Holes W/ insp Window, #4 CLASS B, C AWG, 40 Navy, 5/6 IN Bolt, 8, 346 Index, Gray, Electro Tin Plated.



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	4 AWG
Conductor - Copper DLO Size Range	N/A
Conductor Size	4 AWG
Conductor - Copper Str Navy Size Range	40 (19) Navy-50 (19) Navy
Conductor - Copper Str Navy Size	40 (19) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	4 AWG

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions


Dimension - Pad Width inch	0.56 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/16
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	69 mm
Dimension - Outside Diameter inch	0.34 in
Dimension - Hole Size mm	10 mm
Dimension - Hole Size inch	0.38
Dimension - Stud Size fraction	5/16
Dimension - Bolt Size fraction	5/16
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	13/16 in
Dimension - Z inch	0.37 in
Dimension - B Length inch	0.81 in
Dimension - D inch	1.59 in
Dimension - N inch	0.34 in
Dimension - Inside Diameter inch	0.25 in
Dimension - Bolt Size inch	0.3125
Dimension - Length Overall inch	2.70 in

General

Trade Name	HYLUG™
Die Index	8
Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived
Plated	Y
Color Code	Gray
UPC	781810018101
Type	Standard Barrel, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated

Logistics

Minimum Pack Quantity50



Product Assets

[Catalog \[English\]](#)