



## YA4C2L90, 4 AWG Cu, 2-Hole, 1/4" Stud on .62", Std, 90 Deg

By Burndy

Catalog # [YA4C2L90](#)

4 AWG Cu, 2-Hole, 1/4" Stud on .62" Spacing, Standard Barrel, 90 Degree Pad, Tin Plated



### Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

### Application

Wire Termination

### Specifications

|                               |              |
|-------------------------------|--------------|
| Certification - ETL           | No           |
| Certification - UL Recognized | No           |
| Standards - RoHS Compliance   | CM           |
| Status                        |              |
| Certification - cULus         | No           |
| Industry Standard(s)          | UL 486A-486B |
| UL Listed                     | Yes          |
| Certification - CSA Approved  | Yes          |

### Conductor

|                                   |        |
|-----------------------------------|--------|
| Conductor - Copper DLO Size Range | N/A    |
| Conductor Size                    | 4 AWG  |
| Conductor - Material              | COPPER |
| Conductor Type                    | CODE   |
| Conductor - Copper Str Size Range | 4 AWG  |
| Conductor - Copper Str Size       | 4 AWG  |

### Configuration

|                                      |                 |
|--------------------------------------|-----------------|
| Physical Attribute - Number of Holes | 2               |
| Number of Pad Holes                  | 2               |
| Connector Type                       | STANDARD BARREL |

### Current

|                   |       |
|-------------------|-------|
| Voltage Rating    | 35 kV |
| Voltage - Maximum | 35000 |

### Dimensions

|                                   |           |
|-----------------------------------|-----------|
| Dimension - Pad Width inch        | 0.51 in   |
| Package Height                    | 0.000 in  |
| Dimension - Hole Size fraction    | 1/4       |
| Dimension - Bolt Size fraction    | 1/4       |
| Physical Attribute - Tongue Angle | 90 Degree |
| Dimension - Height inch           | 1.22 in   |
| Dimension - B Length fraction     | 13/16 in  |
| Package Weight                    | 0.000 lb. |
| Package Length                    | 0.000 in  |
| Package Width                     | 0.000 in  |
| Dimension - Z inch                | 0.33 in   |
| Dimension - L Length Overall mm   | 37 mm     |
| Dimension - B Length inch         | 0.81 in   |
| Dimension - Outside Diameter inch | 0.34 in   |
| Dimension - D inch                | 1.21 in   |
| Dimension - N inch                | 0.25 in   |
| Dimension - Inside Diameter inch  | 0.25 in   |
| Dimension - Hole Size mm          | 6.9 mm    |
| Dimension - Bolt Size inch        | 0.25      |
| Dimension - Hole Size inch        | 0.27      |
| Dimension - Length Overall inch   | 1.47 in   |
| Dimension - Strip Length inch     | 7/8       |
| Dimension - Stud Size inch        | 1/4       |
| Dimension - Stud Size fraction    | 1/4       |

### General

|                        |                                                                              |
|------------------------|------------------------------------------------------------------------------|
| Feature - Barrel Type  | Standard                                                                     |
| Feature - Barrel Style | <ul style="list-style-type: none"><li>• Chamfered</li><li>• Skived</li></ul> |
| Plated                 | Y                                                                            |
| Color Code             | Gray                                                                         |
| Trade Name             | HYLUG™                                                                       |
| Die Index              | 8                                                                            |
| UPC                    | 781810317228                                                                 |
| Type                   | Standard Barrel, Tin Plated                                                  |
| Material               | Copper                                                                       |
| Plating Type           | Tin - Electro Plated                                                         |
| Finish Type            | Tin-Plated                                                                   |
| UPC 12 Digit           | 781810317228                                                                 |
| UPC 14 Digit GTIN      | 00781810317228                                                               |

Logistics

|                       |    |
|-----------------------|----|
| Minimum Pack Quantity | 50 |
| Carton Quantity       | 50 |

Temperature Rating194

Product Assets

[Catalog \[English\]](#)

Operational



A Hubbell brand