



YA4C2TC3845, 4 AWG Cu, 2-Hole, 3/8" on 1", Long, 45 Deg

By Burndy

Catalog # [YA4C2TC3845](#)

4 AWG, CU, 2 Hole, 3/8" Stud, 1" Spacing, Long Barrel, 45 Degree Pad, Tin Plated, Gray / 8 or 346 Index



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	4 AWG
Conductor - Copper DLO Size Range	N/A
Conductor Size	4 AWG
Conductor - Copper Str Navy Size Range	40 (19) Navy
Conductor - Copper Str Navy Size	40 (19) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	4 AWG

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2

Connector Type LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.58 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Dimension - Height inch	1.25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	77 mm
Dimension - Outside Diameter inch	0.34 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1-3/16
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	45 Degree
Angle - Pad	45 °
Dimension - B Length fraction	1-1/8 in
Dimension - Z inch	0.43 in
Dimension - B Length inch	1.12 in
Dimension - D inch	1.84 in
Dimension - N inch	0.41 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	3.03 in

General

Trade Name	HYLUG™
Die Index	8
Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived
Plated	Y
Color Code	Gray
Physical Attribute - Tongue Type	Standard

UPC	781810126769
Type	Long Barrel, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810126769
UPC 14 Digit GTIN	00781810126769

Minimum Pack Quantity	50
Carton Quantity	50

Operational

Temperature Rating	194
--------------------	-----

Product Assets

Logistics

[Catalog \[English\]](#)

